



## Etac Fresh bath board

Designed to assist users and carers with every day routines.

 **etac**<sup>®</sup>

Creating Possibilities

# Etac Fresh bath board

Fresh bath board has won a number of awards for its superb design and excellent functionality.

## The original

Fresh has won many design awards and it has set the standard for bath boards in the industry. It's front edge, placed on the bathtub's outer side is wide to provide maximum support for transfers. The midsection is narrowed off to allow ease of access for intimate hygiene. Fresh inner side is designed to give place for soap and shampoo within comfortable reach.

## Secure mounting

The edge 'stops' are easy to mount and secure by using the included plastic coin. Four friction linings make the bath board stay securely on the bathtub. Fresh is available in two lengths to ensure a perfect fit to various bath tubs.



### Support handle

The orange handle design makes it easy to grip.



*Fresh is the original that set the standard for bath boards in the industry with its curved design.*

Description	Edge stop range	Weight	Item no.
Fresh Bath Board - 69 cm 27 <sup>1</sup> / <sub>4</sub> "	From 636 mm to 390 mm	2.1 kg 4.1 lbs	81600011 ✓
Fresh Bath Board - 69 cm 27 <sup>1</sup> / <sub>4</sub> " with Orange Safety Handle	From 636 mm to 390 mm	2.2 kg 4.6 lbs	81600014 ✓
Fresh Bath Board - 69 cm 27 <sup>1</sup> / <sub>4</sub> " with Orange Safety Handle and retail packaging	From 636 mm to 390 mm	2.2 kg 4.6 lbs	81600114 ✓
Fresh Bath Board - 74 cm 29 <sup>1</sup> / <sub>4</sub> "	From 686 mm to 432 mm	2.3 kg 5.1 lbs	81600021 ✓
Fresh Bath Board - 74 cm 29 <sup>1</sup> / <sub>4</sub> " with Orange Safety Handle	From 686 mm to 432 mm	2.3 kg 5.1 lbs	81600024 ✓
Support Handle			81302023

Dimensions	
Width:	36 – 27 – 30 cm 14 <sup>1</sup> / <sub>4</sub> – 10 <sup>3</sup> / <sub>4</sub> – 11 <sup>3</sup> / <sub>4</sub> "
Thickness:	4 cm 1 <sup>1</sup> / <sub>2</sub> "

Material	
Overall:	Polypropylene
Edge stops:	Polypropylene with TPE surface

for maximum of 3 minutes					


  

		<p>Clean the product with a solvent-free cleaning agent (pH level 6–9), or with a 70% disinfectant solution. Can be decontaminated at max. 85°C / 185°F if so required.</p>
--	--	---



 **etac**®  
Creating Possibilities

“Everyone should be able to live a free and independent life and pursue their dreams regardless of any physical circumstances.”

 = Standard Stock Item